

Portable Pipe Elemental Spectrometer



AI Overview

Portable spectrometers allow on-site elemental analysis of metals in pipes, offering fast, accurate, and versatile detection of alloying elements and trace impurities.

Types of Portable Spectrometers

1. Optical Emission Spectrometry (OES) Portable OES devices, such as the ferro.lyte® and Belec Compact Port HLC, use spark excitation to analyze metals directly on-site . They excel at detecting low atomic number elements like carbon, phosphorus, sulfur, boron, and nitrogen, which handheld XRF or LIBS instruments often cannot measure . These spectrometers are ideal for pipe inspection, quality control, and PMI (Positive Material Identification), providing precise alloy composition and supporting standards like API 5L, ASME, and ISO 17025 . They are designed for portability, with intuitive interfaces, battery operation, and adaptable probes for curved or small surfaces . 2. X-ray Fluorescence (XRF) Handheld XRF analyzers, such as the JITA19201, use X-ray excitation to identify metals and alloys quickly . They are lightweight, compact, and capable of analyzing elements like silver, tungsten, and tantalum. XRF is particularly useful for rapid field screening, detecting impurities, and storing large datasets for later analysis. However, XRF is less sensitive to light elements like carbon or nitrogen, which limits its use for full alloy characterization in pipes . 3. Laser-Induced Breakdown Spectroscopy (LIBS) Portable LIBS systems, like the STE-PORTA-LIBS-2000, use a pulsed laser to create plasma on the sample surface, allowing qualitative and quantitative analysis of solids, liquids, and gases . LIBS requires minimal sample preparation and can detect trace elements in real time. It is highly portable and suitable for field applications, though it may have lower precision for certain alloying elements compared to OES.

Key Features for Pipe Analysis

Article Content

Mobile Metal Analyzer

For onsite metal analysis, SPECTRO offers a complete range of mobile metal analyzer products, from handheld XRF to portable Arc

portable spectrometer | Belec

With our specially developed adapters, you can easily analyze even challenging samples such as wires,

Funkenspektrometer für Metallanalyse to go

Das mobile Funkenspektrometer ferro.lyte® erleichtert die mobile Analyse von Metallen. Jetzt mehr über das intuitive OES erfahren!

Portable Elemental Analysis: Niton XL3t Handheld XRF

The Thermo Scientific Niton XL3t XRF analyzer delivers fast, lab-quality elemental analysis in the field,

Analytical Instruments

SPECTRO is a leading supplier of X-ray fluorescence (XRF), ICP-OES/AES, and Arc/Spark-OES instruments for science and

Elemental Analysis with Handheld XRF Analyzers | Bruker

Elemental analysis with Bruker handheld XRF analyzers enables on-the-spot elemental analysis for high concentrations such as

Mobiles Funkenspektrometer ferro.lyte®

Das mobile Funkenspektrometer ferro.lyte mit dem innovativen All-In-One Konzept ist für die präzise

Niton Portable Analyzer Models

Review the many models of Thermo Scientific Niton portable XRF and LIBS analyzers for elemental identification and metal verification.

Mobile Optical Spectrometer | Spark OES | Hitachi High

Looking for a mobile optical emission spectrometer? View our range offering the highest level of accuracy

Portable handheld spectrometers

The SciAps PowerHouse X is a portable benchtop XRF spectrometer that offers on-site elemental analysis. Its 80 kV X-ray tube

Bruker ELIO

Description Portable Micro X-ray Fluorescence Spectrometer The ELIO is a compact and portable energy dispersive X-ray

Handheld/Portable XRF Analyzers for Precise Elemental Analysis

SPECTRO handheld and portable XRF analyzers are rugged, easy-to-use instruments designed for fast, accurate elemental analysis

Portabler Metallanalysator

Ermüdungsarmer Einsatz & Akkubetrieb – mit einer Akkuladung sind bis zu 800 Messungen möglich Bei

Portable Analysis for Material ID

Achieve instant, actionable data with our elemental and radiation detection solutions. Our analyzers enable

Plant elemental composition and portable X-ray fluorescence (pXRF ...

Emergence of portable X-ray fluorescence (pXRF) systems presents new opportunities for rapid, low-cost plant

Portable Metal Analyzer

It accurately analyzes elements such as carbon, sulfur, phosphorus, and boron. It's as fast as an XRF, with

SPECTROTEST

The SPECTROTEST mobile arc spark spectrometer is ideal for many applications in the metal producing,

RFA-Handspektrometer | Bruker

Handheld/Mobile/Portable XRF Spectrometers Handheld / portable X-ray fluorescent (XRF) analyzers have the capability to non

Mobile optical emission spectrometer ferro.lyte®

The optics, the heart of every optical emission spectrometer, are specially designed for use in harsh

TRACER 5 pXRF spectrometer | Bruker

TRACER 5 is the high value in-situ pXRF performer synchronizing power, function, precision and accuracy

S2 PICOFOX

The S2 PICOFOX is a transportable TXRF spectrometer for ultra-trace element analysis. Due to its complete independence of any

Portable XRF Spectrometer 5000 – Handheld Alloy

The AELAB Portable XRF Spectrometer 5000 is a powerful handheld analyzer tailored for quick, accurate

Mobile optical emission spectrometer ferro.lyte®

ferro.lyte® is a mobile spectrometer, optimized for use in metal production, metal processing and metal recycling. It uses the principle

Portable XRF Metal Analyzer

Meet your metal analysis needs anywhere with the JITA19201 Handheld XRF Analyzer. This rugged 245x250x90mm portable

Instruments for optical emission spectrometry (OES)

Advantages of optical emission spectrometry (OES) The advantage of optical emission spectrometry (OES) over other techniques is

Contact Us

For more information, pricing, or custom solutions, please contact us:

Website: <https://www.kilitech.co.za>

Email: info@kilitech.co.za

Phone: +44 20 7183 2649

Address: 1st Floor, The Shard, 32 London Bridge Street, London, SE1 9SG, United Kingdom

This document is for informational purposes only. Specifications subject to change without notice.

